



Film Capacitors – AC Capacitors

Motor run capacitors

Series/Type: Dual Motor Cap™ for washing machine application
Ordering code: B32418S*
Date: 2018-08-16
Version: 2

© EPCOS AG 2018. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Construction

- Metallized polypropylene film
- Plastic case
- Polyurethane
- Dry type

Features

- Self-healing properties
- Low dissipation factor
- High insulation resistance
- Integrated with mounting groove

Typical applications






- For general sine wave applications, mainly as motor run capacitor for washer

Terminals


- Flexible lead wires
- Receptacles on request: crimped to the end of flexible wires


Technical data and specifications

Reference standards	IS 2993	
Safety class to IS 2993	P0	
Life expectancy to IS 2993	440 V/+70 °C: 3000 h (Class C)	
Rated capacitance C_R	See dimension table	
Tolerance	±5%	
Rated voltage V_R	440 V	
Rated frequency f_R	50 Hz	
Maximum ratings		
Maximum permissible voltage V_{max}	1.1 V_R	(V_R = rated voltage)
Maximum permissible current I_{max}	1.3 I_R	(I_R = rated current)

Test data																	
AC test voltage terminal to terminal V_{TT}	2 V_R , 2 s (routine test) 2 V_R , 10 s (type test)																
Insulation voltage terminals to case	2000 Vac																
Insulation resistance R_{is} time constant at + 20°C Rel. Humidity \leq 65 °C (minimum value)	3000 s																
Maximum rate of voltage rise dv/dt_{max}	10 V/ μ s																
Dissipation factor $\tan \delta$ at +20 °C	$\leq 7 \times 10^{-3}$ (1KHz)																
Climatic data																	
Climatic category	25/070/21 to IEC 60068-1																
Lower category T_{min}	-25 °C																
Upper category T_{max}	+70 °C																
Damp heat test t_{test}	21 days																
Mechanical and thermal properties																	
Can and top disk material	Plastic as per IS 2993																
Compatibility to RoHS																	
Compliance to directive 2011/65/EU																	
Marking	<div style="border: 1px solid black; padding: 5px; margin-bottom: 5px;">  <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: center;">$C_x, C_y \mu F$</td> <td style="text-align: center;">V_{RMS}</td> </tr> <tr> <td style="text-align: center;">$T_x \%$</td> <td style="text-align: center;">VAC</td> </tr> <tr> <td style="text-align: center;">25/085/21</td> <td style="text-align: center;">Series</td> </tr> <tr> <td style="text-align: center;">IS 2993</td> <td style="text-align: center;">MPP 'SH'</td> </tr> <tr> <td style="text-align: center;">WW.YY</td> <td style="text-align: center;">PO Number</td> </tr> </table> </div> <div style="border: 1px solid black; padding: 5px; margin-bottom: 5px;"> <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="text-align: center;">IS 2993:1998</td> <td style="text-align: center;">450V D</td> </tr> <tr> <td style="text-align: center;"></td> <td style="text-align: center;">50 Hz</td> </tr> <tr> <td style="text-align: center;">CML-7800031911</td> <td style="text-align: center;">P0</td> </tr> </table> </div> <p>Where, C_x, C_y – Capacitance value V_{RMS} – Rated AC voltage $T_x\%$ –Tolerance on capacitance Series--B32418S WW.YY – Week code PO Number – Internal traceability number</p>	$C_x, C_y \mu F$	V_{RMS}	$T_x \%$	VAC	25/085/21	Series	IS 2993	MPP 'SH'	WW.YY	PO Number	IS 2993:1998	450V D		50 Hz	CML-7800031911	P0
$C_x, C_y \mu F$	V_{RMS}																
$T_x \%$	VAC																
25/085/21	Series																
IS 2993	MPP 'SH'																
WW.YY	PO Number																
IS 2993:1998	450V D																
	50 Hz																
CML-7800031911	P0																


Dimensional drawing



Ordering codes and packing units

Voltage VAC	Capacitance 1 μF	Capacitance 2 μF	Dimension (D + d x L) mm	Ordering code
440	5.3	2.1	40 + 35 x 62	B32418S5745J02*
	7	4	40 + 35 x 62	B32418S5116J02*
	8	4	40 + 35 x 62	B32418S5126J02*
	8	6	40 + 35 x 62	B32418S5146J22*
	10	4	40 + 35 x 62	B32418S5146J02*
	9.5	4	40 + 35 x 62	B32418S5146J52*
	10	5.5	40 + 35 x 62	B32418S5156J52*
	10	5	40 + 35 x 62	B32418S5156J02*
	9	5	40 + 35 x 62	B32418S5146J12*
	9	6	40 + 35 x 62	B32418S5156J12*
	10	6	40 + 35 x 62	B32418S5166J02*
	8.5	5	40 + 35 x 62	B32418S5136J52*

*Indicates wire length which is optional as per customer request

Packaging specification


Dimensions	Unit carton				Master carton			
	$l \pm 10$	$b \pm 10$	$h \pm 10$	Qty	$l \pm 10$	$b \pm 10$	$h \pm 10$	Qty
D x L (mm)								
40 + 35 x 62	465	235	110	50	490	480	240	200

Cautions and warnings

⚠ Please read “Applications warning, installation and maintenance instructions” and the “General Safety Data Sheet for Power Capacitors” issued by ZVEI, which are available on the internet at www.epcos.com/ac_capacitors, to ensure optimum performance and to prevent products from failing, and in worst case, bursting and fire. Information given in the data sheet reflects typical specifications. You are kindly requested to approve our product specifications or request our approval for our specification before ordering.

Display of ordering codes for EPCOS products

The ordering code for one and the same EPCOS product can be represented differently in data sheets, data books, other publications, on the EPCOS website, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under www.epcos.com/orderingcodes

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.

Release 2018-06