

EPCOS Product Brief (India)

Power Quality Solutions

Hybrid Solutions with Harmonic Filtering and
Reactive Power compensation

An ever increasing deployment of high power converters in industrial application causes the grid power quality to deteriorate. The displacement power factor and the current distortion are two key indicators of the quality of the grid power. An active harmonic filter (AHF) alone is capable of addressing both, the low power factor issue as well as the high current distortion issues of power quality. However the higher cost and higher losses associated with the AHF makes the AHF an expensive proposal for addressing multiple power quality problems. In view of this, TDK offers an economical hybrid solution which combines the features of the AHF with those of automatic power factor correction (APFC) capacitors. This hybrid solution offered by TDK ensures high performance and quality of power at much lower costs.



1. Hybrid Solution (Harmonic Filtering and Reactive Power Compensation)

Basic Specifications and Range:

- Complying to Standards IEC-61000 and IS-16636.
- Rated Voltage – 400 ~ 690V.
- Rated Frequency - 50/60Hz.
- 32 bit DSP with 3 Level Topology.
- Floor Mounted Construction.
- Rated Output – 100 KVAR to ~ 2000 KVAR.
- Load balancing and leading compensation.
- Modular Design and low MTTR. Optional provision for future expansion.
- Programmable selective harmonic compensation.
- Communication port RS485.
- Standard Parts Viz, Capacitor, Reactor, Controller, Modules.
- Protections – OV/UV/OC/OT/SC/EF etc.
- Available in thyristor as well as contactor switching configuration.

Features:

- High quality integrated product.
- Effective Thermal Design.
- Unique test facility including harmonic generator.
- All major components under one roof.
- Controllers with easier of programming.
- Less Maintenance.

Applications:

- Best suited in industry for centralized group compensation.
- Industries having VFD and inverter, UPS, etc.
- Industries such as Textile, Paper, Steel, Automobile, IT-parks, Data Centers Hospitals.
- Solar Generation Farms and Wind Mills.

2. Hybrid Solution (Stepless Reactive Power Compensation)

With the invention of switching logic, it is possible to achieve automatic control of reactive power compensation. Despite the means are available of achieving dynamic reactive power compensation, there is limit to have fine control due to fixed step rating in APFC Panel. The need of intermediate fine control of reactive power including real time can be catered through step less switching technology called SVG or Static – VAR – Generator .

The advanced step less technology consists of Active device IGBT. The product can be effectively applied when combined with normal APFC system. This combined Hybrid Solution of (Stepless+Step) switching forms LV SVG system.

The product consists of SVG Modules and LC (Reactor- Capacitor) steps, which are monitored by controlled by Advanced multilevel Controller. The controller effectively utilizes the combination to cater and fine tune the need of reactive power compensation at all the times.

Basic Specifications and Range:

- Complying to Standards IEC-61000.
- Rated Voltage – 400 ~ 690V*.
- Advanced Multicontroller - 18 steps for Thyristor/Contactor switching.
- Module Prototypes – 30 KVAR, 50 KVAR, and 100 KVAR.
- Very fast response time (< 15ms)
- Rated Output – 100 KVAR to ~ 2000 KVAR.

Features:

- Advanced DSP Controller.
- Suitable for inductive and Capacitive Loads.
- Real time reactive power compensation.
- Load Balancing.
- Most suited for reduction in MD.

* 690V available for specific application.

Applications:

- Best suited for Robotic and welding loads.
- Induction furnace startup loads.
- Iron and Steel Rolling Mills.
- High unbalance and highly fluctuating Loads.
- Industries Such as Food, Paper, Commercial Malls.

Benefits:

- Extremely smooth compensation.
- Reduction in electricity bill (MD).
- Avoid network resonance.
- No hunting.

Authorized Dealer



For more details on products and applications please contact our nearest sales office or write to us at sales.in@tdk-electronics.tdk.com

TDK India Pvt. Ltd.

A TDK Group Company
Sales Head Office:
14/2, Rajesh Chambers, Brunton Road, Bengaluru
560001. Tel: +91-80-4039 0640. Fax: +91-80-4039 0603.
Email: sales.in@tdk-electronics.tdk.com

Regional Sales Offices:
Kolkata Tel: +91-33-2419 8815.
Mumbai Tel: +91-22-2575 0800.
Noida Tel: +91-120-4505 815/828.
Bengaluru Tel: +91-80-4039 0640.

Fax: +91-33-2419 8815.
Fax: +91-22-2575 0810.
Fax: +91-120-4505 818.
Fax: +91-80-4039 0603.

"Product development is a continuous process. Consequently the data indicated in this leaflet is subject to change without prior notice. For the latest information, contact your local partners."